



National Defence

Défense nationale

National Defence Headquarters
Ottawa, Ontario
K1A 0K2

Quartier général de la Défense nationale
Ottawa (Ontario)
K1A 0K2

SOLICITATION AMENDMENT

MODIFICATION DE L'INVITATION

**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À :**

Brooke.Monette@forces.gc.ca

Proposal To: National Defence Canada

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Proposition à : Défense nationale Canada

Ce document est par le présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Solicitation No – No de l'invitation : W8474-248421
Solicitation Closes – L'invitation prend fin At – à : 14:00 EDT On - le : 21 July 2023

Amendment No. – No modif. 05	Page 1 of/de 5
Date : 14 July 2023	
Title/Titre Radio Frequency (RF) Shelter, including input/output (I/O) Plate, Electromagnetic Interference (EMI) Hardened Lights, Ventilation System and User Manual	
Address Enquiries to – Adresser toutes questions à brooke.monette@forces.gc.ca	
Telephone No. – N° de téléphone	FAX No – N° de fax
Destination See Herein – Voir ci-inclus	

Instructions:
Municipal taxes are not applicable. Unless otherwise specified herein all prices quoted must include all applicable Canadian customs duties, GST/HST, excise taxes and are to be delivered Delivery Duty Paid including all delivery charges to destination(s) as indicated. The amount of the Goods and Services Tax/Harmonized Sales Tax is to be shown as a separate item.

Instructions: Les taxes municipales ne s'appliquent pas. Sauf indication contraire, les prix indiqués doivent comprendre les droits de douane canadiens, la TPS/TVH et la taxe d'accise. Les biens doivent être livrés « rendu droits acquittés », tous frais de livraison compris, à la ou aux destinations indiquées. Le montant de la taxe sur les produits et services/taxe de vente harmonisée doit être indiqué séparément.

Delivery required - Livraison exigée	Delivery offered - Livraison proposée
Vendor Name and Address - Raison sociale et adresse du fournisseur	
Name and title of person authorized to sign on behalf of vendor (type or print) - Nom et titre de la personne autorisée à signer au nom du fournisseur (caractère d'imprimerie)	
Name/Nom _____	Title/Titre _____
Signature _____	Date _____

Amendment 05

The purpose of RFP W8474-248421 Amendment 05 is to:

1. Update the RFP as below; and,
2. Facilitate the third round of questions and answers.

1- At PART 4 – EVALUATION PROCEDURES AND BASIS OF SELECTION, subsection 4.1.1.1. Mandatory Technical Criteria, MTC 4 EMI Hardened Lights:

Delete:

The EMI Hardened Lights must:

- a. Provide a minimum of 500 lux through out the entire shelter;
- b. Be capable of operating on 110/240 VAC 50/60HZ; and,
- c. Meet the following military standards. "MIL-STD-461, DEF STAN 59/411, MIL-STD-704, MIL-STD-1275, and MIL-STD-1399.

Insert:

The EMI Hardened Lights must:

- a. Provide a minimum of 500 lux through out the entire shelter;
- b. Be capable of operating on 110/240 VAC 50/60HZ; and,
- c. Meet the following military standard, "MIL-STD-461".

2- At ANNEX "A" - REQUIREMENT, Subsection 4.1.1.4 EMI Hardened Lights Specifications:

Delete:

The EMI Hardened Lights must:

- a. Provide a minimum of 500 lux through out the entire shelter;
- b. Be capable of operating on 110/240 VAC 50/60HZ; and,
- c. Meet the following military standards. "MIL-STD-461, DEF STAN 59/411, MIL-STD-704, MIL-STD-1275, and MIL-STD-1399.

Insert:

The EMI Hardened Lights must:

- a. Provide a minimum of 500 lux through out the entire shelter;
- b. Be capable of operating on 110/240 VAC 50/60HZ; and,
- c. Meet the following military standard, "MIL-STD-461,".

3- At PART 4 – EVALUATION PROCEDURES AND BASIS OF SELECTION, subsection 4.1.1.1. Mandatory Technical Criteria, MTC 1 RF Shelter i.:

Delete:

- i. Include transport cases adhering to the STANAG 4280 and DEF-STAN 81-41 standards for military use; and,

Insert:

- i. Include transport cases; and,

4- At ANNEX “A” - REQUIREMENT, Subsection 4.1.1.1 RF Shelter Specifications i.:

Delete:

- i. Include transport cases adhering to the STANAG 4280 and DEF-STAN 81-41 standards for military use; and,

Insert:

- i. Include transport cases; and,

Q1

Within the RFP at PART 4 – EVALUATION PROCEDURES AND BASIS OF SELECTION, subsection 4.1.1.1. Mandatory Technical Criteria, MTC 4 EMI Hardened Lights and at ANNEX “A” REQUIREMENT, Subsection 4.1.1.4, EMI Hardened Lights Specifications, it is stated that:

“The EMI Hardened Lights must:

- a. Provide a minimum of 500 lux through out the entire shelter;
- b. Be capable of operating on 110/240 VAC 50/60HZ; and,
- c. Meet the following military standards. “MIL-STD-461, DEF STAN 59/411, MIL-STD-704, MIL-STD-1275, and MIL-STD-1399.”

Would DND Accept EMI hardened Lights which emit EMI from inverters outside of the enclosure? The EMI emitted from the inverters outside the enclosure would not affect the environment inside of the enclosure.

A1

Yes

Q2

Within the RFP at PART 4 – EVALUATION PROCEDURES AND BASIS OF SELECTION, subsection 4.1.1.1. Mandatory Technical Criteria, MTC 4 EMI Hardened Lights c. and at ANNEX “A” REQUIREMENT, Subsection 4.1.1.4, EMI Hardened Lights Specifications c., it is stated that:

“The EMI Hardened Lights must:

- c. Meet the following military standards. “MIL-STD-461, DEF STAN 59/411, MIL-STD-704, MIL-STD-1275, and MIL-STD-1399.”

Must the EMI Hardened Lights meet all of the standards listed at c.?

A2

Please see the modified required specifications at point 1 and 2 above.

Q3

Would Canada Extend the closing date and time of the RFP to a revised date of 17 July 2023?

A3

Please see RFP Amendment 04.

Q4

Within the RFP at PART 4 – EVALUATION PROCEDURES AND BASIS OF SELECTION, subsection 4.1.1.1. Mandatory Technical Criteria, MTC 1 RF Shelter i., and at ANNEX “A” REQUIREMENT, RF Shelter Specifications i., it is stated that “The RF Shelter must include transport cases adhering to the STANAG 4280 and DEF-STAN 81-41 standards for military use”.

As we are having difficulty finding a tent frame case meeting both STANAG 4280 and DEF-STAN 81-4 standards, would Canada accept a solution with two (2) transport cases? One (1) case for the tent frame which does not meet STANAG 4280 and DEF-STAN 81-4 standards and one (1) transport case for the tent which does meet STANAG 4280 and DEF-STAN 81-4 standards.

A4

Yes, please see the modifications to the RFP at points 3 and 4 above.

Q5

Within the RFP at PART 4 – EVALUATION PROCEDURES AND BASIS OF SELECTION, subsection 4.1.1.1. Mandatory Technical Criteria, MTC 4 EMI Hardened Lights c. and at ANNEX “A” REQUIREMENT, Subsection 4.1.1.4, EMI Hardened Lights Specifications c., it is stated that:

“The EMI Hardened Lights must:

- c. Meet the following military standards. “MIL-STD-461, DEF STAN 59/411, MIL-STD-704, MIL-STD-1275, and MIL-STD-1399.”

Would Canada accept EMI Hardened Lights which comply only with MIL-STD461?

A5

Yes. Please see the modified required specifications at point 1 and 2 above.

ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED